D3 Micro

Automatically Disinfects Door Handles



www.hyso.com

The D3 Micro kills flu virus and 99.9% of germs* to help protect people at a critical point of cross-contamination – the door handle.

The most cost-effective way to disinfect door handles, and the only way to do it automatically. The D3 Micro is the only Environmental Protection Agency (EPA) registered automated system for disinfecting door handles.



Cost-Effective

- Refill canister lasts for up to 100 days
- Ambient light sensor saves battery and canister life

Programmable

- Adjustable spray frequency (15, 30 or 60 minutes)
- Day or 24-hour interval settings

Liquid Crystal Display

 Instant indication of battery strength and refill canister level

Easy to Install and Maintain

- Works with your existing door hardware
- Mounts in minutes with no special tools or wiring required
- Refill canisters can be replaced in seconds

Alcohol and Quat-Based Formula

- Quick-drying, anti-microbial mist
- Disinfects the entire door handle including the underside

Aesthetics

- Cutting-edge design
- Presents a professional image

*Kills Influenza A2, MRSA, Rhinovirus, Norovirus, Salmonella, Pseudomonas and Staphylococcus aureus.


EPA REG. NO. 1839-85-83326 EPA EST. NO. 074216-IL-001 **D3 Micro - Devices**


D3 Micro – Refill Formula (6/case)

<u>Stock #</u> <u>Description</u> 441110......EPA Formula (4.5oz) 441120.......EU Formula (175ml)

D3 Micro

Specifications







CONTROL PANEL & LCD DISPLAY

- (1) ON/OFF Switch
- (2) DAY/24H Switch

 DAY = Unit powers down when lights off
 - **24H** = Unit operates 24 hours per day
- (3) 15/30/60 Switch
 - Sets the unit to spray every **15, 30 or 60** minutes
- (4) Reset Button
 - Test Spray: Press for 1 second

Reset LCD Refill Can Status: Press/hold

for 3 seconds

- (5) Light Sensor
 - Allows the unit to power down when lights are off (DAY setting)
- (6) Red Warning Light

Flashes when the proximity sensor detects a person or object (to indicate that the unit will not spray)

Flashes when refill canister needs to be replaced

(7a) Battery Life Indicator

(7b) Refill Can Status

Refill Canister Life

NOTE: Approximately 800 sprays per can

_		Hours facility open and D3 Micro in use				
		8	12	24		
Spray	15	25 Days	17 Days	8 Days		
requency	30	50 Days	34 Days	17 Days		
(Minutes)	60	100 Days	68 Days	34 Days		

Battery Life

NOTE: Approximately 8,000 sprays per set of 3 AA batteries

	Hours facility open and D3 Micro in use				
		8	12	24	
Spray	15	8 Months	6 Months	3 Months	
Frequency	30	1.5 Years	1 Year	6 Months	
(Minutes)	60	3 Years	2 Years	1 Year	

- Dimensions: H 7.40" (188mm), D 2.64" (67mm), W 4.37" (111mm)
- Available in White or Black
- Easily mounts with either 2 screws or industrial-strength double-sided tape (both included)
- 3-year limited warranty



Corporate Headquarters:

HYSO LLC 15 W 37th St, 7th Floor New York, NY 10018-6223 1-888-HYSO-LLC (1-888-497-6552)

Contacts:

North American Sales: sales@hyso.com International Sales: internationalsales@hyso.com Product Support: productsupport@hyso.com

Media Inquiries: press@hyso.com